



Ortronics

Cisco GLC-2BX-D-20 Compatible 1000Base-BX 2 Channel CSFP Transceiver (SMF, Tx: 1490nm Rx: 1310nm, 20km, LC Duplex, DDM, I-Temp)
Part No. GLC-2BX-D-20-L



Cisco GLC-2BX-D-20 Compatible 1000Base-BX 2 Channel CSFP Transceiver (SMF, Tx: 1490nm Rx: 1310nm, 20km, LC Duplex, DDM, I-Temp)

Features & Benefits

Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Connector Type	LC Duplex
Wavelength	1310nm	Form Factor	SFP