



Ortronics

Cisco GLC-ZX-SM-RGD Compatible 1000Base-ZX SFP Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

Part No. GLC-ZX-SM-RGD-L



Cisco GLC-ZX-SM-RGD Compatible 1000Base-ZX SFP Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

Features & Benefits

Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

Full Service Technical Support

Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Connector Type	LC Duplex
Wavelength	1550nm	Form Factor	SFP