



Force10 GP-QSFP-40GE-11R Compatible 40GBase-PLR4 (4x10GBase-LR) QSFP+ Transceiver (SMF, 1310nm, 10km, MPO/MTP, DDM, C-Temp)



## Features & Benefits

Guaranteed Compatible  
In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty  
For more information by product line, visit our Warranty page.

Full Service Technical Support  
Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate  
Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate  
Extensive inventory guarantees same day shipping.

## Specifications

### General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	0 C
Operating Temperature Max	70 C	Data Transfer Rate	10 Gbps
Connector Type	MPO	Wavelength	1310nm