



Fujitsu HCD25D10I0000-0 Compatible 25GBase-LR Dual Rate SFP28 Transceiver (SMF, 1310nm, 10km, LC Duplex, DDM, I-Temp)



Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our [Warranty](#) page.
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info			
Product Line	Ortronics	UPC Number	662875065760
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		
Dimensions			
Product Width US	13.9 mm	Product Depth US	58.4 mm
Product Height US	12.6 mm		
Technical Information			
Fiber Optic Cable Type	Single-Mode	Max Distance Support	10 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Connector Type	LC Duplex		