



Clarity Cat 5E, CAT6 & CAT6A High Density Jack, ETL verified to TIA Category 5E, 6 & 6A component specification. Rear-loading, 180° exit, 8 position. Quick and easy lacing cap termination. Universal T568A/B wiring label. Center tuned to Clarity 5E patch cords for optimum performance.

Features & Benefits

| | |
|---|--|
| Guaranteed Performance levels ETL verified to TIA Category 6a & 6 component specification. | Lacing Cap Design No punch tool required, quick termination and installation time. |
| Rear loading Preferred mounting for panels. | Icon compatible, C6a & Cat6 marking on jack face Supports 606 designation requirements. |
| RoHS compliant Lead free. | Easy to follow universal wiring label Quick and user-friendly, eliminates confusion. |
| Center tuned design Transparent interface with Clarity 6a & 6 patch cords. | High density footprint Supports 48 port 1RU panel applications. |
| Supports PoE IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4 | |

Specifications

General Info

| | | | |
|-------------------|--------|--------------|---|
| Color | Black | UPC Number | 662875880837 |
| Country Of Origin | Mexico | Product Line | Legrand |
| Type | Jack | Standard | TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant |

Technical Information

| | | | |
|---------------------|---|------------------------|------------|
| Shielded/Unshielded | Unshielded | Compatibility | 568A/B |
| PoE Specs | IEEE 802.3af, 802.3at, 802.3bt Type 1 through 4 | Operating Temperature | -40 + 70 C |
| Gauge | 22-26 AWG | Performance Level/Tier | Cat 6a |
