



Clarity Cat 5E, CAT6 & CAT6A High Density Jack, ETL verified to TIA Category 5E, 6 & 6A component specification. Rear-loading, 180° exit, 8 position. Quick and easy lacing cap termination. Universal T568A/B wiring label. Center tuned to Clarity 5E patch cords for optimum performance.

## Features & Benefits

Guaranteed Performance levels ETL verified to TIA Category 6a & 6 component specification.	Lacing Cap Design No punch tool required, quick termination and installation time.
Rear loading Preferred mounting for panels.	Icon compatible, C6a & Cat6 marking on jack face Supports 606 designation requirements.
RoHS compliant Lead free.	Easy to follow universal wiring label Quick and user-friendly, eliminates confusion.
Center tuned design Transparent interface with Clarity 6a & 6 patch cords.	High density footprint Supports 48 port 1RU panel applications.
Supports PoE IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4	

## Specifications

### General Info

Color	Red	UPC Number	662875880844
Country Of Origin	Mexico	Product Line	Legrand
Type	Jack	Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant

### Technical Information

---

Shielded/Unshielded	Unshielded	Compatibility	568A/B
---------------------	------------	---------------	--------

---

PoE Specs	IEEE 802.3af, 802.3at, 802.3bt Type 1 through 4	Operating Temperature	-40 + 70 C C
-----------	---	-----------------------	--------------

---

Gauge	22-26 AWG	Performance Level/Tier	Cat 6a
-------	-----------	------------------------	--------

---