



Clarity High Density Jack (HDJ) CAT6A, T568A/B, White Part No. HDJ6A-88



Clarity Cat 5E, CAT6 & CAT6A High Density Jack, ETL verified to TIA Category 5E, 6 & 6A component specification. Rear-loading, 180° exit, 8 position. Quick and easy lacing cap termination. Universal T568A/B wiring label. Center tuned to Clarity 5E patch cords for optimum performance.

Features & Benefits

Guaranteed Performance levels

ETL verified to TIA Category 6a & 6 component specification.

Rear loading

Preferred mounting for panels.

RoHS compliant

Lead free.

Center tuned design

Transparent interface with Clarity 6a & 6 patch cords.

Supports PoE

IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4

Lacing Cap Design

No punch tool required, quick termination and installation time.

Icon compatible, C6a & Cat6 marking on jack face

Supports 606 designation requirements.

Easy to follow universal wiring label

Quick and user-friendly, eliminates confusion.

High density footprint

Supports 48 port 1RU panel applications.

Specifications

General Info

Color	Cloud White	UPC Number	662875880899
Country Of Origin	Mexico	Product Line	Legrand
Type	Jack	Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant

Technical Information

Shielded/Unshielded	Unshielded	Compatibility	568A/B
PoE Specs	IEEE 802.3af, 802.3at, 802.3bt Type 1 through 4	Operating Temperature	-40 + 70 C
Gauge	22-26 AWG	Performance Level/Tier	Cat 6a