



## Clarity High Density Jack (HDJ) CAT6A, T568A/B, Fog White, 25 Pack Part No. HDJ6A25

Clarity Cat 5E, CAT6 & CAT6A High Density Jack, ETL verified to TIA Category 5E, 6 & 6A component specification. Rear-loading, 180° exit, 8 position. Quick and easy lacing cap termination. Universal T568A/B wiring label. Center tuned to Clarity 5E patch cords for optimum performance.

### Features & Benefits

#### Guaranteed Performance Levels

ETL verified to TIA Category 6a & 6 component specification.

#### Rear loading

Preferred mounting for panels.

#### RoHS compliant

Lead free.

#### Center tuned design

Transparent interface with Clarity 6a & 6 patch cords.

#### Supports PoE

IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4

#### Lacing Cap Design

No punch tool required, quick termination and installation time.

#### Icon compatible, C6a & Cat6 marking on jack face

Supports 606 designation requirements.

#### Easy to follow universal wiring label

Quick and user-friendly, eliminates confusion.

#### High density footprint

Supports 48 port 1RU panel applications.

### Specifications

#### General Info

|                   |           |              |  |
|-------------------|-----------|--------------|--|
| Color             | Fog White | UPC Number   | 662875301936   |
| Country Of Origin | Mexico    | Product Line | Legrand  |
| Type              | Jack      | Standard     | ANSI/TIA-568-C.2, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant |

#### Technical Information

|                     |            |                        |        |
|---------------------|------------|------------------------|--------|
| Shielded/Unshielded | Unshielded | Compatibility          | 568A/B |
| Gauge               | 22-26 AWG  | Performance Level/Tier | Cat 6a |