



Clarity High Density Jack (HDJ) CAT6A, T568A/B, White, 25 Pack Part No. HDJ6A25-88

Clarity Cat 5E, CAT6 & CAT6A High Density Jack, ETL verified to TIA Category 5E, 6 & 6A component specification. Rear-loading, 180° exit, 8 position. Quick and easy lacing cap termination. Universal T568A/B wiring label. Center tuned to Clarity 5E patch cords for optimum performance.

Features & Benefits

Guaranteed Performance Levels

ETL verified to TIA Category 6a & 6 component specification.

Rear loading

Preferred mounting for panels.

RoHS compliant

Lead free.

Center tuned design

Transparent interface with Clarity 6a & 6 patch cords.

Supports PoE

IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4

Lacing Cap Design

No punch tool required, quick termination and installation time.

Icon compatible, C6a & Cat6 marking on jack face

Supports 606 designation requirements.

Easy to follow universal wiring label

Quick and user-friendly, eliminates confusion.

High density footprint

Supports 48 port 1RU panel applications.

Specifications

General Info

| | | | |
|-------------------|-------------|--------------|------------------------------------------------------------------------------------------------------------------------------|
| Color | Cloud White | UPC Number | 662875301974 |
| Country Of Origin | Mexico | Product Line | Legrand |
| Type | Jack | Standard | ANSI/TIA-568-C.2, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant |

Technical Information

| | | | |
|------------------------|------------|---------------|-----------|
| Shielded/Unshielded | Unshielded | Compatibility | 568A/B |
| Operating Temperature | -40 + 70 C | Gauge | 22-26 AWG |
| Performance Level/Tier | Cat 6a | | |