



Ortronics Clarity Shielded High Density Jack (HDJS) CAT6, T568A/B Part No. HDJS6

Shielded Clarity High Density Jacks incorporate mechanical and electrical advancements to provide industry leading protection against EMI, with electrical and data transmission performance headroom, and a simple termination method. The easy to lace and crimp termination reduces time to install, while maintaining cable performance. These jacks are rear loading, utilizing an innovative locking latch for quick reliable mounting and removal.



Features & Benefits

| | |
|---|--|
| Circuit traces: Each circuit trace is rated to 100W, 1.5A | Superior Protection Against EMI: Minimizes disturbances in data transmission |
| Enhances PoE heat dissipation: Ideal for high-power PoE applications | Lacing cap termination: Reduces wiring time for faster installations |
| Accepts color ID icons: Perfect for port identification or segmentation | Versatile mounting: Use at both ends of the channel, compatible with patch panels, wall plates, furniture plates, surface mount boxes and more |
| High density footprint: Mount up to 48 ports per 1RU | Rear loading: Preferred mounting for panels |
| Plenum Rated to UL 2043: Can be installed in any air handling space | |

Specifications

General Info

| | | | |
|--------------|--------------|--------------------|-----------------------|
| UPC Number | 662875020066 | Country Of Origin | Mexico |
| Product Line | Legrand | Application Sector | Commercial/Industrial |
| Type | Jack | Standard | UL Standard |

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|