



Clarity Shielded High Density Jack (HDJS) CAT6A, T568A/B, 25 pack Part No. HDJS6A25

Shielded Clarity High Density Jacks incorporate mechanical and electrical advancements to provide industry leading protection against EMI, with electrical and data transmission performance headroom, and a simple termination method. The easy to lace and crimp termination reduces time to install, while maintaining cable performance. These jacks are rear loading, utilizing an innovative locking latch for quick reliable mounting and removal.

Features & Benefits

Circuit traces: Each circuit trace is rated to 100W, 1.5A	Superior Protection Against EMI: Minimizes disturbances in data transmission
Enhances PoE heat dissipation: Ideal for high-power PoE applications	Lacing cap termination: Reduces wiring time for faster installations
Accepts color ID icons: Perfect for port identification or segmentation	Versatile mounting: Use at both ends of the channel, compatible with patch panels, wall plates, furniture plates, surface mount boxes and more
High density footprint: Mount up to 48 ports per 1RU	Rear loading: Preferred mounting for panels
Plenum Rated to UL 2043: Can be installed in any air handling space	

Specifications

General Info

UPC Number	662875020059	Country Of Origin	Mexico
Product Line	Legrand	Application Sector	Commercial/Industrial
Type	Jack	Standard	UL Standard

Additional Information

RoHS Conformant	Yes
-----------------	-----