




radiant Collection
radiant® Multi-Location Remote Dimmer, White
Part No. HMRWCCV4



Provides precise dimming control of a light or fixture from another part of the room through this second on-wall controller. Must be used with the Multi-Location Master Dimmer. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Installs easily with 3-way wiring for multi-location dimming. For use with most Incandescent, CFL/LED (with the exception of 0 - 10v options) and MLV dimmable bulbs.
- Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.
- Constant memory features returns lights to their previous level after a power failure or outage.
- No derating required in multi-gang applications.
- Features durable, high-impact resistant thermoplastic construction.
- More color options available. (For Tri-Color version: Includes three interchangeable face plates in white, light almond, and ivory for flexible customization.)
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Features	Indicator Lights
Switch Type	Paddle	Number of Switches	1
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US	4.25 in
-------------------	---------

Technical Information

Number of Gangs	1	Amperage	15 A
Bulb Compatibility	CFL, Incandescent, LED	Number of Poles	3-Way, Multi-Location, Single Pole
Wattage	700 W	Mounting Type	Box
Voltage	120.0 V		