



Pass and Seymour
Discontinued - Specification Isolated Grade Quads, Orange
Part No. IG420



Isolated Ground Quad Receptacle 20A 125V Orange

Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007125658	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Number of Wires	3	Temperature Rating	-40° - 65° C
-----------------	---	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Environmental Conditions	Flammability: UL94 V2 and UL94-5 VA