

Turnlok® Duplex Receptacle 3-Wire 15A 125V Isolated Ground



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength. Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

IG symbol and Isolated Ground markings for easy identification and circuit delineation. One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands. Side and external screw-pressure-plate backwire capability. Accepts #14-#10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007647006
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Phase	3	Number of Wires	3
Number of Poles	Double Pole	Wire Size	0-18Awg
Voltage	125 V		