



Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 250volt Orange

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant plated steel strap.

Patented feature, external screw-pressure-plate back wire Plastic barrier isolates grounding terminal from mounting strap clamp on ground terminal for faster, easier installation. and metal boxes.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid Auto-ground clip assures positive ground. or stranded wire.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Orange	UPC Number	785007242867
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	250 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10
Number of Wires	3	Environmental Conditions	Flammability: UL94 V2
