



Resealable package of 25 Category 6 Keystone jack, 8-position, 180 degree exit, icon compatible, T568A/B wiring, Blue. Keystone, KT2Jjacks and modules feature New installer friendly lacing cap termination with free termination tool in every carton. The keystone footprint allows flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before and during the construction process.

## Features & Benefits

|   |  |
|---|--|
| Rear loading: Preferred mounting for panels.  | Icon compatible, C5e marking on jack face: Supports 606 designation requirements.  |
| Free termination tool in each carton of 20 jacks: Convenient no extra termination tool required.  | RoHS compliant: Lead free.   |
| Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.   | Lacing Cap Design: No punch tool required, quick termination and installation time.  |
| Always Ready for Install: Each package of jacks includes 1 standard lacing cap termination tool (Compatible with any HDJ or KT2 jacks). | Enhanced ergonomics: Optional high durability metal, lacing cap termination tool makes install easier, improving bulk installation and sustainability. Part Number: HDJHCT |
| Replacement plastic lacing cap termination tools, part number: HDJPCT-4PK   |  |

## Specifications

### General Info

|                   |  |                    |                        |
|-------------------|--|--------------------|------------------------|
| Product Line      | Ortronics  | UPC Number         | 662875882923           |
| Country Of Origin | Mexico   | Application Sector | Commercial, Industrial |
| Standard          | TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4, FCC part 68 Subpart F, IEC-603-7 compliant | Type               | Jack                   |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 0.56 in | Product Depth US | 1.23 in |
|------------------|---------|------------------|---------|

---

Product Height US    0.63 in

---

**Additional Information**

---

RoHS Compliant        Yes

---