



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase

Features & Benefits

Individual Patch Cable Assembly – Standard Insertion Loss
0.30 dB Insertion loss

Single-mode total channel connection loss: 2.1 dB

Cable Size
All configurations below are 2mm duplex zipcord - other configuration options available

Polarization
A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable

Compliance
BAA or TAA

Part of a Standard Loss System
When combined with Infinium Core Trunks and Infinium Core Cassettes

Single-mode total channel connection return loss: 49 dB

Fiber Type
Supports Single-Mode OS2 Fiber

Jacket Color
Yellow - other configuration options available

Specifications

General Info

Product Line	Ortronics	Country Of Origin	Mexico
Type	Fiber Patch Cord		

Technical Information

Jacket Application	Plenum Rated	Simplex/Duplex	Duplex
Jacket Rating	OFNP Rated, FT6 Rated		