



Turnlok® Connector 3-Wire 20A 125/250V



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	3-Way
Wire Size	18 - 10 AWG	Voltage	125.0 V

---