

Turnlok Single Receptacle 3wire 30amp 125/250v



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
 One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
 Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
 Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.
 Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
 Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Color	Black	UPC Number	785007103052
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Poles	3-Way	Voltage	125 V
Phase	3	Wire Size	10-18Awg
Number of Wires	3		