



Pass and Seymour  
Turnlok® Receptacle 3W 30A 125V/250V  
Part No. L1030R

Turnlok® Single Receptacle 3-Wire 30A 125/250V



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                       |                         |                    |  |
|-----------------------|-------------------------|--------------------|--|
| Product Line          | Pass & Seymour          | Color              | Black                                  |
| UPC Number            | 785007103052            | Country Of Origin  | Mexico                                 |
| Number of Receptacles | 1                       | Features           | Brass Mounting Strap, Impact Resistant |
| Outlet Type           | Locking                 | Application Sector | Commercial                             |
| Wall Plate Included   | No                      | Standard           | UL 498                                 |
| Warranty Type         | 1-Year Limited Warranty |                    |  |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.61 in | Product Depth US | 3.48 in |
|------------------|---------|------------------|---------|

|                   |         |
|-------------------|---------|
| Product Height US | 1.28 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                      |                 |                         |             |
|----------------------|-----------------|-------------------------|-------------|
| Connection Location  | Back and Side   | Phase                   | Three       |
| Number of Wires      | 3               | Amperage                | 30 A        |
| Number of Poles      | 3-Way           | Wire Size               | 14 - 10 AWG |
| Indoor/Outdoor       | Indoor          | NEMA Configuration Code | L10-30R     |
| Wire Connection Type | Screw Terminals | Voltage                 | 125/250 V   |