



Turnlok® Single Receptacle 3-Wire 30A 125/250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007103052	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	1.61 in	Product Depth US	3.48 in
Product Height US	1.28 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	3-Way
Wire Size	18 - 10 AWG	Voltage	125.0 V
