



Pass and Seymour  
20A NEMA Connector L1120, Black Back, White Front Body  
Part No. L1120C

Turnlok® Connector 3-Wire 20A 3-Phase 250V



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material. Rounded back contour reduces snags and hang-ups on the job site.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Scalloped shell design provides non-slip gripping surface for insertion and withdrawal. Visible stamped NEMA configuration and device rating.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	2.2 in	Product Length US	3.33 in
------------------	--------	-------------------	---------

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	3-Way
Wire Size	18 - 10 AWG	Voltage	125.0 V

---