



Connector 3-Wire 30A 480V Turnlok®



## Features & Benefits

|   |  |
|---|--|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.           | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.                                |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock.               | Double dovetail design provides superior protection against cord pull-out forces.  |
| Impact- and corrosion-resistant durable nylon 6 shell material.                             | Rounded back contour reduces snags and hang-ups on the job site.   |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal.       | Visible stamped NEMA configuration and device rating.  |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

## Specifications

### General Info

|                    |                |                   |           |
|--------------------|----------------|-------------------|-----------|
| Product Line       | Pass & Seymour | Color             | Black     |
| UPC Number         | 785007123012   | Country Of Origin | Mexico    |
| Application Sector | Industrial     | Standard          | UL Listed |

### Dimensions

|                  |        |                   |         |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 3.33 in |
|------------------|--------|-------------------|---------|

### Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

Technical Information

|          |       |                 |             |
|----------|-------|-----------------|-------------|
| Phase    | Three | Number of Wires | 3           |
| Amperage | 30 A  | Number of Poles | Double Pole |

---