



Turnlok® Connector 4-Wire 30A 125/250V

Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scalloped shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007143010 | Country Of Origin | Mexico |
| Application Sector | Industrial | Standard | UL 498 |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|---|-----------------|-------------|
| Number of Wires | 3 | Number of Poles | Double Pole |
|-----------------|---|-----------------|-------------|

Wire Size

4

Voltage

125 V
