



Pass and Seymour

20 Amp NEMA Plug L1820 - Black Back, White Front Body
Part No. L1820P

Plug 4wire 20amp 120/208volt Turnlok



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock. Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material. Rounded back contour reduces snags and hang-ups on the job site.
- Scalloped shell design provides non-slip gripping surface for insertion and withdrawal. Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention. Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Color Black UPC Number 785007182040

Country Of Origin Mexico Product Line Pass & Seymour

Application Sector Industrial Standard UL 498

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Poles 3-Way Voltage 120 V

Phase 3 Wire Size 0-18Awg

Number of Wires 4