



ANGLE ADAPTER 20/30A 3W TURNLOCK

## Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

Angle adapters (sold separately) will accommodate all P&S Turnlok style plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.

Angle plugs and adapters have the same wide cord diameter range (.230" - 1.150") that is present on all Turnlok plugs and connectors.

20/30A 3 Wire Turnlok: Right Angle Adapters are adjustable up to 8 positions.

Tri-drive assembly and cord-grip screws are standard on all angle plugs and adapters.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007165449	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL498

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	#18 - #8

---

Environmental Conditions      Flammability: UL94 V2: Operating  
Temperature: Maximum continuous +115°C,  
minimum -40°C without impact

---