



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase.

## Features & Benefits

Part of a Ultra- Low Loss System: When combined with Infinium Ultra Trunks and Infinium Ultra Cassettes

Flexible Polarity: A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable

Compliance: BAA or TAA Compliant

Bend-insensitive fiber for optimal cable management and ease of installation

Dust caps pre-installed

TIA Channel Compliant

## Specifications

### General Info

Product Line	Ortronics	Color	Aqua
Country Of Origin	United States	Type	Fiber Patch Cord

### Dimensions

Product Length US	1.0 m	Cable Length	1 m
-------------------	-------	--------------	-----

### Technical Information

Fiber Optic Cable Type	OM4	Jacket Material	PVC
Compatibility	Infinium acclAIM	Jacket Application	Plenum Rated
Simplex/Duplex	Duplex	Cable Type	Fiber Optic
Jacket Rating	FT6 Rated, OFNP Rated	Attenuation	0.15 dB

---

Cable Diameter

2 mm

Performance Level/Tier

Infinium Ultra

---