



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase

## Features & Benefits

Part of a Quantum – Low Loss System When combined with Infinium Quantum Trunks and Infinium Quantum Cassettes	Flexible Polarity A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable
Compliance BAA or TAA Compliant	Dust caps pre-installed
Bend-insensitive fiber for optimal cable management and ease of installation	TIA Channel Compliant

## Specifications

### General Info

Product Line	Quiktron	Color	Yellow
Country Of Origin	United States		

### Dimensions

Cable Length	10 ft
--------------	-------

### Technical Information

Fiber Optic Cable Type	OS2	Cable Type	Duplex
Attenuation	0.14 dB	Performance Level/Tier	Infinium Quantum
Storage Temperature	-40 C, 70 C		