



Pass and Seymour  
30A NEMA L630 Plug - Black Back, White Front Body  
Part No. L630P

Turnlok® Plug 3-Wire 30A 250V



## Features & Benefits

- |   |  |
|---|--|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.           | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.                                |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock.               | Double dovetail design provides superior protection against cord pull-out forces.  |
| Impact- and corrosion-resistant durable nylon 6 shell material.                             | Rounded back contour reduces snags and hang-ups on the job site.   |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal.       | Visible stamped NEMA configuration and device rating.  |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

### Dimensions

Product Depth US	2.57 in	Product Length US	2.57 in
------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Wires	3	Amperage	30 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	4
-----------------	-------------	-----------	---

Voltage	250.0 V
---------	---------