

Turnlok Single Receptacle, 3wire 30amp 277volt



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

UPC Number	785007273052	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Commercial
Standard	UL 498		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Poles	Double Pole	Voltage	277 V
Phase	3	Wire Size	10-18Awg
Number of Wires	3		
