



Industrial Spec Grade SingleTurnlok® 20A 480V Receptacle

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007282054
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL498, CSA C22.2 No. 42		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection	Back and side wire	Number of Wires	3
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	480 V	Environmental Conditions	Flammability: UL94 V2: Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact
