



Wattstopper
LI Enclosure w/24 Relay Capacity Interior, Surface Mount
Part No. LENC24S



LENC panel enclosures are designed specifically to work with all configurations of LMCP panel interiors containing 8 to 48 relays. The enclosures are provided with integral mounting studs that are configured to accept the panel interior making the installation quick and easy. Covers are secured to the tubs with screws and have keyhole style mounting. This allows the cover to be temporarily hung on the tub during the construction phase of the project. All covers have hinged doors that expose only the low voltage (Class 2) section of the panel and are equipped with key locks and two keys each. All LENC enclosures are NEMA 1 rated. Consult factory for other NEMA rated applications.

Features & Benefits

- 16-gauge all steel tubs with galvineal finish
- Surface mounting with back mounting holes, screw cover
- Studs provided for quick installation of panel interior section
- Screw on, powder coated cover permits temporary hanging via key hole screw slots
- Lockable door access to Class 2 panel section, meets NFPA 70
- UL and cUL listed; five year warranty

Specifications

General Info

UPC Number	754182926152	Country Of Origin	United States
Product Line	Wattstopper		

Technical Information

Enclosure Type	Steel
----------------	-------