



Q-Series M2 Standard Density Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution enables industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Q-Series Rack Mount or Wall Mount Fiber Enclosures.

Features & Benefits

Low Loss System

When combined with Infinium Core Trunks and Infinium Core Patch Cords Total System Loss 2.5 dB Total Return Loss 19 dB

Infinium Core

• Single-mode total channel connection loss: 2.1 dB • Single-mode total channel connection return loss: 49 dB • Multimode total channel connection loss: 2.5 dB • Multimode total channel connection return loss: 19 dB

High Density

12 or 24-fiber cassette compatible with Q-Series Enclosures

Fiber Type

Supports either Single-mode OS2 or Multimode Infinium Core fiber

Polarization

Universal

LC adapter with Internal shutter

Provides eye safety by attenuating laser light when the mated connector is removed • 100% automatic shutter mechanism requiring no operator handling of the shutter door • Compatible with standard LC connectors • It keeps adapter's interior clean from dust • You can see the visible light through the adapter

Specifications

General Info

UPC Number	662875031024	Country Of Origin	United States
Product Line	Legrand	Application Sector	Commercial
Type	Cassette	Standard	TIA-568-C.3

Additional Information

RoHS Conformant	Yes
-----------------	-----