



Legrand
DLM Color Control Timer Switch, Grey
Part No. LMTS-101-CCT-G



The LMTS-101-CCT from Wattstopper allows building occupants to enjoy the benefits of Human Centric Lighting by automatically adjusting Correlated Color Temperature (CCT) on a scheduled cycle throughout the day. It can make any building environment feel more visually comfortable by automatically replicating the inviting feeling of natural daylight, but is especially well-suited for commercial offices, healthcare, and educational facilities. The interface is designed to work with light fixtures that are enabled for tunable white with Blanco and Araya logic modules (also from Wattstopper). Notes: Switches do not include face plates. Order decorator style plate separately.

Features & Benefits

Low Voltage CCT Timer Switch The LMTS-101-CCT from Wattstopper allows building occupants to enjoy the benefits of Human Centric Lighting by automatically adjusting Correlated Color Temperature (CCT) on a scheduled cycle throughout the day. It can make any building environment feel more visually comfortable by automatically replicating the inviting feeling of natural daylight, but is especially well-suited for commercial offices, healthcare, and educational facilities. The interface is designed to work with light fixtures that are enabled for tunable white with Blanco and Araya logic modules (also from Wattstopper). Notes: Switches do not include face plates. Order decorator style plate separately.

Sleek single gang device fits decorator wall plates Programming buttons hidden behind override button

Low-profile styling with the choice of five decorator colors and compatible with decorator wall plates High resolution screen for all schedule entries

LED indicator for visibility in darkened rooms Programmable button to manually control connected load or override the schedule

Specifications

General Info

Color Gray

UPC Number 754182940660

Countries Of Origin China

Product Line Wattstopper

Dimensions

Product Volume US 19.84 cu in

Product Width US 2.0 in

Product Height US 2.1 in

Product Weight US 0.3 lb

Product Depth US 4.5 in