



## Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Electromagnetic and radio-frequency interference protection built in.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

## Specifications

### General Info

**Color** Ivory

**UPC Number** 785007157963

**Countries Of Origin** China

**Product Line** Pass & Seymour

**Application Sector** Residential

**Type** Dimmer

**Standard** UL Listed

### Listing Agencies / 3rd Party Agencies

**cULus Listed** Yes

**cULus ListingNumber** 95219

### Technical Information

---

<b>Wattage</b>	1000 W
<b>Number of Poles</b>	Single Pole
<b>Voltage</b>	120 V
<b>Load</b>	1000 Watt
<b>Operating Cycles</b>	100000

---