



Pass and Seymour
LS Series Incandescent Slide Dimmer, Black
Part No. LS1000PBK



Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Electromagnetic and radio-frequency interference protection built in.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Superior heat management.

No derating on 600W units.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Black	UPC Number	785007045529
-------	-------	------------	--------------

Country Of Origin	China	Product Line	Pass & Seymour
-------------------	-------	--------------	----------------

Application Sector	Residential	Type	Dimmer
--------------------	-------------	------	--------

Standard	UL Listed
----------	-----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	95219
--------------	-----	---------------------	-------

Technical Information

Wattage	1000 W	Number of Poles	Single Pole
---------	--------	-----------------	-------------

Voltage	120 V	Load	1000 Watt
---------	-------	------	-----------

Operating Cycles	100000
------------------	--------