



Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Electromagnetic and radio-frequency interference protection built in.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Superior heat management.

No derating on 600W units.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Ivory

UPC Number 785007157994

Countries Of Origin China

Product Line Pass & Seymour

Application Sector Residential

Type Dimmer

Standard UL Listed

Technical Information

Wattage 1000 W

Number of Poles Single Pole

Voltage 120 V

Load 1000 Watt

Operating Cycles	100000
------------------	--------
