



Incandescent Slide Dimmer, Non-Preset 1000W, White



## Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Electromagnetic and radio-frequency interference protection built in.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

## Specifications

### General Info

|                    |                |                         |           |
|--------------------|----------------|-------------------------|-----------|
| Product Line       | Pass & Seymour | Replaced by Part Number | LS600W    |
| Color              | White          | Country Of Origin       | China     |
| Application Sector | Residential    | Standard                | UL Listed |
| Type               | Dimmer         |                         |           |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

Technical Information

|                  |             |          |           |
|------------------|-------------|----------|-----------|
| Operating Cycles | 100000      | Amperage | 8.3 A     |
| Number of Poles  | Single Pole | Wattage  | 1000 W    |
| Voltage          | 120.0 V     | Load     | 1000 Watt |

---