



## Legrand

LS TradeMaster CFL/LED/Incandescent Single-Pole, Non-Preset Dimmer, Brown

Part No. LSCL450



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

### Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers).

Built-in electromagnetic and radio-frequency interference protection.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent

No dirt-catching crevices.

Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting.

Superior heat management.

Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz.

### Specifications

#### General Info

UPC Number 785007040494

Countries Of Origin China

Product Line Pass & Seymour

Application Sector Residential

Type Dimmer

Standard cULus, RoHS

#### Technical Information

Wattage 450 W

Number of Poles Single Pole

Voltage 120 V

Connection Screw Terminals

---

**Frequency Rating** 120VAC 60Hz Hz

---

**Load** CFL/LED/Incandescent

---

**Environmental Conditions** Humidity: Less than 95% non condensing

---