



Pass and Seymour
LS TradeMaster CFL/LED/Incandescent Single-Pole, Non-Preset Dimmer, Light Almond
Part No. LSCL450LA



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers).	Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent
Built-in electromagnetic and radio-frequency interference protection.	No dirt-catching crevices.
Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models.	Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting.
Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.	Superior heat management.
Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.	Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz.

Specifications

General Info

UPC Number	785007040470	Country Of Origin	China
Product Line	Pass & Seymour	Application Sector	Residential
Type	Dimmer	Standard	cULus, RoHS

Technical Information

Wattage	450 W	Number of Poles	Single Pole
Voltage	120 V	Connection	Screw Terminals

Frequency Rating

120VAC 60Hz Hz

Load

CFL/LED/Incandescent

Environmental Conditions

Humidity: Less than 95% non
condensing
