



Pass and Seymour
LS Series CFL/LED/Incandescent Single Pole Slide Dimmer, Non-Preset, White
Part No. LSCL450W



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Works with dimmable CFL/LED or Incandescent lighting loads at 450W CFL/LED & 700W Incandescent
Built-in electromagnetic and radio-frequency interference protection	No dirt-catching crevices
Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plates available for all models	Preset ON/OFF switch automatically returns controlled lights to preset level without re-adjusting dimmer setting
Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts	Superior heat management
Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer	Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Features	Locator Light
Switch Type	Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, RoHS
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.19 in		

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Bulb Compatibility	CFL, Incandescent, LED	Number of Poles	Single Pole
Wattage	700 W	Voltage	120.0 V
Load	LED, Incandescent, CFL	Environmental Conditions	Humidity: Less than 95% non condensing