



Pass and Seymour
LS Series CFL/LED/Incandescent 3-Way Slide Dimmer, Non-Preset, Black
Part No. LSCL453PBK



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, scullpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Single pole/3-way versions
Unique integrated single pole/3-way dimmer control	Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Features	Locator Light
Switch Type	Push, Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, RoHS
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.19 in		

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
------------------	--------------	------------	-----------------

Bulb Compatibility	CFL, Incandescent, LED	Number of Poles	3-Way
Wattage	700 W	Voltage	120.0 V
Load	CFL, Incandescent, LED	Environmental Conditions	Humidity: Less than 95% non condensing