



Pass and Seymour  
LS Series CFL/LED/Incandescent 3-Way Slide Dimmer, Non-Preset, Light Almond  
Part No. LSCL453PLA



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

## Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)

Single pole/3-way versions

Unique integrated single pole/3-way dimmer control

Rating: 450W LED & CFL: 700W Incandescent: 120VAC  
60Hz

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007040500
Country Of Origin	China	Features	Low-End Trim (Dim Range)
Switch Type	Rocker, Single Pole 3-Way, Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, RoHS
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

### Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.19 in		

Technical Information

Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Minimum Load Recommendation	10 W
Bulb Compatibility	CFL, Halogen, Incandescent, LED	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Trim/Adjustment Level	Wheel
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC	Environmental Conditions	Humidity: Less than 95% non condensing