



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers). Single pole/3-way versions.

Unique integrated single pole/3-way dimmer with fan speed control. Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz.

Specifications

General Info

Color	Brown	UPC Number	785007040456
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Standard	RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Wattage	450 W	Number of Poles	3-Way
Voltage	120 V	Connection	Back & Side Wired
Contact Rating	120VAC	Speed Range	3-Speed
Environmental Conditions	Indoor Only		