



Legrand

LS TradeMaster Single-Pole/3-Way Preset Dimmer w/ Single-Pole/3-Way, 3-Speed De-Hummer Fan Control, Black

Part No. LSCLDC163PBK



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers).

Single pole/3-way versions.

Unique integrated single pole/3-way dimmer with fan speed control.

Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz.

Specifications

General Info

Color Black

UPC Number 785007040432

Countries Of Origin China

Product Line Pass & Seymour

Application Sector Residential

Standard RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Wattage 450 W

Number of Poles 3-Way

Voltage 120 V

Connection Back & Side Wired

Contact Rating 120VAC

Speed Range 3-Speed

Environmental Conditions Indoor Only
