



Pass and Seymour
LS Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer with Single Pole/3-Way, 3-Speed De-Hummer Fan Control, Preset, Light Almond
Part No. LSCLDC163PLA



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Single pole/3-way versions
Unique integrated single pole/3-way dimmer with fan speed control	Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz

Specifications

General Info			
Product Line	Pass & Seymour	Color	Light Almond
Finish	Gloss	UPC Number	785007040562
Country Of Origin	China	Product Series	Trademaster
Features	Combination, De-Hummer Fan Control, Low-End Trim (Dim Range)	Switch Type	Rocker, Slider
Number of Switches	2	Application Sector	Residential
Standard	RoHS	Warranty Type	Limited Lifetime Warranty

Dimensions			
Product Width US	2.5 in	Product Depth US	1.28 in
Product Height US	4.19 in		

Listing Agencies / 3rd Party Agencies	
cULus Listed	Yes

Technical Information			
Preset	Yes	Load Rating	120V 1.25A 150W (CFL), 120V 1.25A 150W (LED), 120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Connection	Back and side wire	Contact Rating	120VAC
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Speed Range	3-Speed	Voltage	120 VAC
Load Type	CFL, Fan Motor, Halogen, Incandescent, LED	Environmental Conditions	Indoor Only