



Pass and Seymour  
LS Series Dual Fan Speed Control/Dimmer, Light Almond  
Part No. LSDC163PLAV



## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Gloss	UPC Number	785007238839
Country Of Origin	China	Features	Combination, De-Hummer Fan Control, Low-End Trim (Dim Range)
Switch Type	Rocker, Single Pole 3-Way, Slider	Number of Switches	2
Application Sector	Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Preset	Yes	Load Rating	120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)
Operating Cycles	100000	Dimming Compatibility	Forward Phase

Frequency Rating	60 Hz	Number of Gangs	1
Bulb Compatibility	Incandescent	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Flying Leads	Voltage	120 VAC