



Pass and Seymour
LS Series Fan Speed Control/Dimmer, Brown
Part No. LSDC16V



Dual Slide 3-Speed De-Hummer Fan Control with Single-Pole Dimmer

Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Device comes with wired leads.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Gloss	UPC Number	785007277678
Country Of Origin	China	Features	Low-End Trim (Dim Range), Combination, De-Hummer Fan Control
Switch Type	Single Pole, Slider	Number of Switches	2
Application Sector	Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	109655	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Load Rating	120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)	Operating Cycles	100000
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	Incandescent
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Button	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Flying Leads	Voltage	120 VAC