



Pass and Seymour
LS Trademaster Incandescent Slide Dimmer and Switch, Black
Part No. LSDS300PBKV



LS Series Slide Dimmers and Fan Speed Controls reflect Legrand innovation and dependability, and give you the ability to control your lighting and save energy. And with two functions in one, you can do more without having to cut into the wall.

Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in control.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Patented Snap-In Light Module (TM8LMCC, sold separately) transforms the dimmer into an illuminated dimmer.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007238945	Country Of Origin	China
Application Sector	Residential	Standard	RoHS, CSA Listed, cULus, UL Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60Hz Hz	Connection	Screw Terminals
Number of Poles	Single Pole	Wattage	300 W
Voltage	120 V	Load	Incandescent
Environmental Conditions	Humidity: Less than 95% non condensing		
