



Pass and Seymour
LS Series Fan Speed Control, Black
Part No. LSSC5PBK

Decorator Slide Fan Control, Preset/3-Speed/5A



Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007045567
Country Of Origin	China	Features	Fan Control, Preset
Application Sector	Residential	Standard	UL/CSA Listed

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	100000	Amperage	5 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Mounting Type	Box		
